



MSD Platinum (Touring/Stage)

MSD Platinum 21 R 1CT/8

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Product data

General Information			
Cap-Base	-[-]		
Operating Position	UNIVERSAL [Any or Universal (U)]		
Main Application	Stage/Touring		
Life To 50% Failures (Nom)	1500 h		
System Description	Reflector-E21.4		
Light Technical			
Color Code	2		
Luminous Flux (Min)	14100 lm		
Luminous Flux (Nom)	15600 lm		
Chromaticity Coordinate X (Max)	312		
Chromaticity Coordinate X (Min)	282		
Chromaticity Coordinate X (Nom)	297		
Chromaticity Coordinate Y (Max)	315		
Chromaticity Coordinate Y (Min)	285		

Chromaticity Coordinate Y (Nom)	300
Correlated Color Temperature (Nom)	8000 K
Luminous Efficacy (rated) (Nom)	33 lm/W
Color Rendering Index (Nom)	-
Operating and Electrical	
Power (Rated) (Nom)	470 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	-
Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C

Datasheet, 2017, August 17 data subject to change

MSD Platinum (Touring/Stage)


Pinch Temperature (Max)	350 °C
Product Data	
Full product code	871869667826800
Order product name	MSD Platinum 21 R 1CT/8
EAN/UPC - Product	8718696678268
Order code	928197805314

Numerator - Quantity Per Pack	1		
Numerator - Packs per outer box	8		
Material Nr. (12NC)	928197805314		
Net Weight (Piece)	110.000 g		

Warnings and Safety


• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing



Product	D (max)	0	C (max)
MSD Platinum 21 R 1CT/8	54 mm	1.2 mm	60 mm

Photometric data





MSD

MSD Platinum (Touring/Stage)



Distributor:



Phone: 407-857-8770 Fax: 407-857-8771

Email: sales@techni-lux.com